



ATA207528014

Trunking 20x75,L=2,0m,brown

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 20 mm

Length 2000 mm

Trunking width 74 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 7

Maximum number of cables (Ø 11 mm, 50% fill) 7

Cover, door

Lid shape premounted

Materials

Colour brown

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Number of wires 1,5 mm² - 40% filling degree 89

Internal/useful cross section 1296 mm²

Number of wires 2,5 mm² - 40% filling degree 71

Equipment

Number of fix dividers 2

Cable retainers per meter 2

Standards

European directive RoHS voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature

-5...65 °C