




ATA207539010



**External corner for ATHEA trunking 20x75mm in pure white**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 20 mm

Length 26.5 mm

Trunking width 74 mm

**Cover, door**

Lid with softlip No

**Materials**

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 83 / 140 °

**Accessories included**

Accessory configuration Moulded

**Standards**

Approvals EN50085-2-1

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

**Use conditions**

Operating temperature

-5...60 °C

**temperatur**

---

Ambient temperature

-5...60 °C