



ATA207548014

Internal corner for ATHEA trunking 20x75mm in brown

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 20 mm

Length 54 mm

Trunking width 75 mm

Cover, door

Lid with softlip No

Materials

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 83 / 140 °

Accessories included

Accessory configuration Moulded

Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

