



ATA207559010



## Flat corner for ATHEA trunking 20x75mm in pure white

### Technical properties

#### Architecture

Fixing mode Clipped

#### Configuration

Antibacterial treatment No

#### Dimensions

Trunking height 20 mm

Length 100 mm

Trunking width 74 mm

#### Cover, door

Lid with softlip No

#### Materials

RAL colour RAL 9010 - Pure white

Type of surface treatment untreated

#### Installation, mounting

Base punching Without base punching

#### Settings

Angle range 90 °

#### Accessories included

Accessory configuration Moulded

#### Standards

Approvals EN50085-2-1

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

#### Use conditions

Operating temperature -5...60 °C

#### temperatur

Ambient temperature -5...60 °C