



ATA630009010

Trunking 6x32,pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	6 mm
Length	2100 mm
Trunking width	32 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	0
Maximum number of cables (Ø 11 mm, 50% fill)	0

Cover, door

Lid shape	premounted
-----------	------------

Materials

RAL colour	RAL 9010 - Pure white
Material	PVC
Material group	plastic
Type of surface treatment	untreated
Transparent	No

Cable

Number of wires 1,5 mm ² - 40% filling degree	6
Internal/useful cross section	170 mm ²
Number of wires 2,5 mm ² - 40% filling degree	6

Equipment

Number of fix dividers	0
Number of plugable separators	0

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP40
---------------------	------

Use conditions

Operating temperature

-5...65 °C