



BA725025BL

Slotted panel trunking made of PVC BA7 25x25mm blue

Technical properties

Architecture

Flexible No

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 25 mm

Length 2000 mm

Trunking width 25 mm

Slot width 6 mm

Tongue width 6.5 mm

Cover, door

Lid shape loose

Materials

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching EN 50085-2-3:1999

Cable

Number of wires 1,5 mm² - 40% filling degree 10

Internal/useful cross section 275 mm²

Number of wires 2,5 mm² - 40% filling degree 7

Number of wires 1,0 mm² - 40% filling degree 14

Standards

European directive RoHS voluntary compliance

UL 94 classification V0

Safety

Fireproof classification M1

temperatur

