



BA760060BL

Slotted panel trunking made of PVC BA7 60x60mm blue

Technical properties

Architecture

Flexible No

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 60 mm

Length 2000 mm

Trunking width 60 mm

Slot width 6 mm

Tongue width 6.5 mm

Cover, door

Lid shape loose

Materials

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching EN 50085-2-3:1999

Cable

Number of wires 1,5 mm² - 40% filling degree 102

Internal/useful cross section 2708 mm²

Number of wires 2,5 mm² - 40% filling degree 73

Number of wires 1,0 mm² - 40% filling degree 142

Standards

European directive RoHS voluntary compliance

UL 94 classification V0

Safety

Fireproof classification M1

temperatur

