



BA7A40100

**Slotted panel trunking made of PVC BA7A 40x100mm grey**

**Technical properties**

**Architecture**

Flexible No

**Configuration**

Side wall configuration Slotted

**Electric current**

Current leak stable Yes

**Dimensions**

Trunking height 40 mm

Length 2000 mm

Trunking width 100 mm

Slot width 6 mm

Tongue width 6.5 mm

**Cover, door**

Lid shape loose

**Materials**

Colour stone grey

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching EN 50085-2-3:1999

**Cable**

Number of wires 1,5 mm<sup>2</sup> - 40% filling degree 91

Internal/useful cross section 2668 mm<sup>2</sup>

Number of wires 2,5 mm<sup>2</sup> - 40% filling degree 65

Number of wires 1,0 mm<sup>2</sup> - 40% filling degree 127

**Standards**

European directive RoHs voluntary compliance

UL 94 classification V0

**Safety**

Fireproof classification M1

