



BA7A60040

Slotted panel trunking made of PVC BA7A 60x40mm grey

Technical properties

Architecture

Flexible No

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 60 mm

Length 2000 mm

Trunking width 40 mm

Width of installed product 40 mm

Slot width 6 mm

Tongue width 6.5 mm

Cover, door

Lid shape loose

Materials

Colour stone grey

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching EN 50085-2-3:1999

Cable

Number of wires 1,5 mm² - 40% filling degree 66

Internal/useful cross section 1758 mm²

Number of wires 2,5 mm² - 40% filling degree 47

Number of wires 1,0 mm² - 40% filling degree 91

Standards

European directive RoHs voluntary compliance

UL 94 classification V0

Safety

temperatur

Ambient temperature

-5...60 °C