



BA7A80060

Slotted panel trunking made of PVC BA7A 80x60mm grey

Technical properties

Architecture

Flexible	No
----------	----

Configuration

Side wall configuration	Slotted
-------------------------	---------

Electric current

Current leak stable	Yes
---------------------	-----

Dimensions

Trunking height	80 mm
-----------------	-------

Length	2000 mm
--------	---------

Trunking width	60 mm
----------------	-------

Slot width	6 mm
------------	------

Tongue width	6.5 mm
--------------	--------

Cover, door

Lid shape	loose
-----------	-------

Materials

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Base punching	EN 50085-2-3:1999
---------------	-------------------

Fixing type	bottom punching
-------------	-----------------

Cable

Number of wires 1,5 mm ² - 40% filling degree	152
--	-----

Internal/useful cross section	3848 mm ²
-------------------------------	----------------------

Number of wires 2,5 mm ² - 40% filling degree	109
--	-----

Number of wires 1,0 mm ² - 40% filling degree	211
--	-----

Standards

Approvals	EN50085-2-3
-----------	-------------

European directive RoHs	voluntary compliance
-------------------------	----------------------

UL 94 classification	V0
----------------------	----

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Fireproof classification	M1
temperatur	
Ambient temperature	-5...60 °C