



BA7A80080

Slotted panel trunking made of PVC BA7A 80x80mm grey

Technical properties

Architecture

Flexible No

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 80 mm

Length 2000 mm

Trunking width 80 mm

Slot width 6 mm

Tongue width 6.5 mm

Cover, door

Lid shape loose

Materials

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching EN 50085-2-3:1999

Fixing type bottom punching

Cable

Number of wires 1,5 mm² - 40% filling degree 206

Internal/useful cross section 5198 mm²

Number of wires 2,5 mm² - 40% filling degree 148

Number of wires 1,0 mm² - 40% filling degree 287

Standards

Approvals EN50085-2-3

European directive RoHs voluntary compliance

UL 94 classification V0

Safety

| | |
|--------------------------|------------|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |
| Fireproof classification | M1 |
| temperatur | |
| Ambient temperature | -5...60 °C |