



BRAP0802ELN

Alu-trunking lid 80, anodised

Technical properties

Configuration

Antibacterial treatment	No
Tamperproof fixing	No

Compatibility

Product compatibility	BRAP
-----------------------	------

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Length	2000 mm
--------	---------

Cover, door

Lid mounting	Internal
Lid with softlip	No
Lid width	80 mm
Cover attachment	Snapped on

Materials

Colour	aluminium
Material	Aluminium
Material group	aluminium

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Use conditions

Operating temperature	-5...90 °C
-----------------------	------------