



BRAP651001ELN

Alu-trunking base 65x100, anodised

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Device installation compatible format	Standard 60mm, CEE, Ecoline, EIB
---------------------------------------	----------------------------------

Connectivity

Trunking coupling	Junction pins as separate reference
-------------------	-------------------------------------

Dimensions

Trunking height	65 mm
Length	2000 mm
Trunking width	100 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	10 / 28
--	---------

Cover, door

Lid mounting	Internal
Lid width	80 mm
Number of lids mountable	1

Materials

Colour	aluminium
Material	Aluminium
Material group	aluminium

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Cable

Internal/useful cross section	5400 mm ²
-------------------------------	----------------------

Equipment

Number of plugable separators	1
Compartment quantity	1 / 2

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Use conditions

