



BRAP651001ELN



Alu-trunking base 65x100, anodised

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Device installation compatible format Standard 60mm, CEE, Ecoline, EIB

Connectivity

Trunking coupling Junction pins as separate reference

Dimensions

Trunking height 65 mm

Length 2000 mm

Trunking width 100 mm

Capacity

Maximum number of cables (\varnothing 11 mm, 50% fill) 10 / 28

Cover, door

Lid mounting Internal

Lid width 80 mm

Number of lids mountable 1

Materials

Material group aluminium

Installation, mounting

Base punching Without base punching

Cable

Internal/useful cross section 5400 mm²

Equipment

Number of plugable separators 1

Compartment quantity 1 / 2

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free	Yes
Impact strength	IK08
Use conditions	
Operating temperature	-5...90 °C