



BRAP651301ELN

## Alu-trunking base 65x130, anodised

### Technical properties

#### Configuration

Antibacterial treatment No

#### Compatibility

Device installation compatible format Standard 60mm, CEE, Ecoline, EIB

#### Connectivity

Trunking coupling Junction pins as separate reference

#### Dimensions

Trunking height 65 mm

Length 2000 mm

Trunking width 130 mm

#### Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 19 / 37

#### Cover, door

Lid mounting Internal

Lid width 80 mm

Number of lids mountable 1

#### Materials

Colour aluminium

Material Aluminium

Material group aluminium

#### Installation, mounting

Base punching Without base punching

#### Cable

Internal/useful cross section 7200 mm<sup>2</sup>

#### Equipment

Number of plugable separators 1

Compartment quantity 1 / 2

#### Standards

European directive RoHS voluntary compliance

#### Use conditions

