



BRAP651301ELN



**Alu-trunking base 65x130, anodised**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Compatibility**

Device installation compatible format Standard 60mm, CEE, Ecoline, EIB

**Connectivity**

Trunking coupling Junction pins as separate reference

**Dimensions**

Trunking height 65 mm

Length 2000 mm

Trunking width 130 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 19 / 37

**Cover, door**

Lid mounting Internal

Lid width 80 mm

Number of lids mountable 1

**Materials**

Material group aluminium

**Installation, mounting**

Base punching Without base punching

**Cable**

Internal/useful cross section 7200 mm<sup>2</sup>

**Equipment**

Number of plugable separators 1

Compartment quantity 1 / 2

**Standards**

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free	Yes
Impact strength	IK08
<b>Use conditions</b>	
Operating temperature	-5...90 °C