



BRAP651701ELN

## Alu-trunking base 65x170, anodised

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

Device installation compatible format	Standard 60mm, CEE, Ecoline, EIB
---------------------------------------	----------------------------------

#### Connectivity

Trunking coupling	Junction pins as separate reference
-------------------	-------------------------------------

#### Dimensions

Trunking height	65 mm
Length	2000 mm
Trunking width	170 mm

#### Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	32 / 50
--	---------

#### Cover, door

Lid mounting	Internal
Lid width	80 mm
Number of lids mountable	1

#### Materials

Colour	aluminium
Material	Aluminium
Material group	aluminium

#### Installation, mounting

Base punching	Without base punching
---------------	-----------------------

#### Cable

Internal/useful cross section	9600 mm <sup>2</sup>
-------------------------------	----------------------

#### Equipment

Number of plugable separators	1
Compartment quantity	1 / 2

#### Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

#### Use conditions

