



BRAP802001ELN



**Alu-trunk. base 80x200,2-comp,anodised**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Compatibility**

Device installation compatible format Standard 60mm, CEE, Ecoline, EIB

**Connectivity**

Trunking coupling Junction pins as separate reference

**Dimensions**

Trunking height 80 mm

Length 2000 mm

Trunking width 200 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 56 / 75

**Cover, door**

Lid mounting Internal

Lid width 80 mm

Number of lids mountable 2

**Materials**

Material group aluminium

**Installation, mounting**

Base punching Without base punching

**Cable**

Internal/useful cross section 14250 mm<sup>2</sup>

**Equipment**

Compartment quantity 2 / 4

Cable retainers per meter 0

**Standards**

European directive RoHS voluntary compliance