



BRP6510019010



**Trunking base,65100,pure white**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Compatibility**

Device installation compatible format Standard 60mm, CEE, Ecoline, EIB

**Connectivity**

Trunking coupling Couplers as separate reference

**Dimensions**

Trunking height 70 mm

Length 2000 mm

Trunking width 100 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 12 / 33

**Cover, door**

Lid mounting Internal

Lid width 80 mm

Number of lids mountable 1

**Materials**

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching With base punching

**Cable**

Internal/useful cross section 5300 mm<sup>2</sup>

**Equipment**

Compartment quantity 1 / 2

Cable retainers per meter 0

**Standards**

European directive RoHS voluntary compliance

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-5...60 °C
<b>temperatur</b>	
Ambient temperature	-5...65 °C