



BRP651004HLAN



Internal corner for BRP/BRHP/BRAP 65x100mm halogen free alu finish

Technical properties

Architecture

Fixing mode	Clamping
-------------	----------

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	BRP/ BRAP
-----------------------	-----------

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	65 mm
Length	135 mm
Trunking width	100 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

Colour	aluminium
Material	PC-ABS
Material group	plastic
Type of surface treatment	Painted

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	85 / 95 °
-------------	-----------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP40
REACH conform	Yes
RoHS conform	Yes

Halogen free	Yes
Impact strength	IK07
Use conditions	
Operating temperature	-30...90 °C
temperatur	
Ambient temperature	-30...90 °C