



BRP651004HLAN

Internal corner for BRP/BRHP/BRAP 65x100mm halogen free alu finish

Technical properties

Architecture

Fixing mode Clamping

Configuration

Antibacterial treatment No

Compatibility

Product compatibility BRP/ BRAP

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 65 mm

Length 135 mm

Trunking width 100 mm

Cover, door

Lid with softlip -

Materials

Colour aluminium

Material PC-ABS

Material group plastic

Type of surface treatment Painted

Installation, mounting

Base punching Without base punching

Settings

Angle range 85 / 95 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHs voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature

-30...90 °C

temperatur

Ambient temperature

-30...90 °C