



BRP651005HLAN

**Flat angle for wall trunking BRP/BRHP/BRAP 65x100mm halogen free alu finish**

**Technical properties**

**Architecture**

Fixing mode Clamping

**Configuration**

Antibacterial treatment No

**Compatibility**

Product compatibility BRP / BRAP

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 65 mm

Length 185 mm

Trunking width 100 mm

**Cover, door**

Lid with softlip -

**Materials**

Colour aluminium

Material PC-ABS

Material group plastic

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 90 °

**Accessories included**

Accessory configuration Moulded

**Standards**

European directive RoHS voluntary compliance

**Safety**

Impact strength IK07

**Use conditions**

Operating temperature -30...90 °C

