



BRP6513019010



Trunking base,65130,pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Device installation compatible format	Standard 60mm, CEE, Ecoline, EIB
---------------------------------------	----------------------------------

Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

Dimensions

Trunking height	65 mm
Length	2000 mm
Trunking width	130 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	20 / 40
--	---------

Cover, door

Lid mounting	Internal
Lid width	80 mm
Number of lids mountable	1

Materials

RAL colour	RAL 9010 - Pure white
Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	With base punching
---------------	--------------------

Cable

Internal/useful cross section	6800 mm ²
-------------------------------	----------------------

Equipment

Compartment quantity	1 / 2
Cable retainers per meter	0

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-5...60 °C
temperatur	
Ambient temperature	-5...65 °C