



BRP651303H9010

**External corner for BRP/BRHP/BRAP 65x130mm halogen free in pure white**

**Technical properties**

**Architecture**

Fixing mode Clamping

**Configuration**

Antibacterial treatment No

**Compatibility**

Product compatibility BRP/ BRAP

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 68 mm

Length 40 mm

Trunking width 130 mm

**Cover, door**

Lid mounting External

Lid with softlip -

Number of lids mountable 1

**Materials**

Colour pure white

RAL colour RAL 9010 - Pure white

Material PC-ABS

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 85 / 95 °

**Accessories included**

Accessory configuration Moulded

**Standards**

European directive RoHS voluntary compliance

**Safety**

Protection index IP	IP40
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-30...90 °C
<b>temperatur</b>	
Ambient temperature	-30...90 °C