



BRP651304H9010



Internal corner for BRP/BRHP/BRAP 65x130mm halogen free in pure white

Technical properties

Architecture

Fixing mode	Clamping
-------------	----------

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	BRP / BRAP
-----------------------	------------

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	65 mm
Length	135 mm
Trunking width	130 mm

Cover, door

Lid with softlip	-
Number of lids mountable	0

Materials

RAL colour	RAL 9010 - Pure white
Material	PC-ABS
Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	85 / 95 °
-------------	-----------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP40
REACH conform	Yes

RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07
Use conditions	
Operating temperature	-30...90 °C
temperatur	
Ambient temperature	-30...90 °C