



BRP651304HLAN

## Internal corner for BRP/BRHP/BRAP 65x130mm halogen free alu finish

### Technical properties

#### Architecture

Fixing mode Clamping

#### Configuration

Antibacterial treatment No

#### Compatibility

Product compatibility BRP / BRAP

#### Connectivity

Trunking coupling without coupler

#### Dimensions

Trunking height 65 mm

Length 135 mm

Trunking width 130 mm

#### Cover, door

Lid with softlip -

#### Materials

Colour aluminium

Material PC-ABS

Material group plastic

Type of surface treatment untreated

#### Installation, mounting

Base punching Without base punching

#### Settings

Angle range 85 / 95 °

#### Accessories included

Accessory configuration Moulded

#### Standards

European directive RoHs voluntary compliance

#### Safety

Impact strength IK07

#### Use conditions

Operating temperature

-30...90 °C

**temperatur**

---

Ambient temperature

-30...90 °C