



BRP651305H9010

Flat angle for wall trunking BRP/BRHP/BRAP 65x130mm halogen free in pure white

Technical properties

Architecture

Fixing mode Clamping

Configuration

Antibacterial treatment No

Compatibility

Product compatibility BRP/BRAP

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 65 mm

Length 185 mm

Trunking width 130 mm

Cover, door

Lid with softlip -

Number of lids mountable 0

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material PC-ABS

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHS voluntary compliance

Safety

Protection index IP IP40

temperatur

Ambient temperature

-30...90 °C