



BRP6517019010



Trunking base,PVC,65170,pure white

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Device installation compatible format Standard 60mm, CEE, Ecoline, EIB

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Trunking height 65 mm

Length 2000 mm

Trunking width 170 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 38 / 57

Cover, door

Lid mounting Internal

Lid width 80 mm

Number of lids mountable 1

Materials

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 9000 mm²

Equipment

Compartment quantity 1 / 2

Cable retainers per meter 0

Standards

European directive RoHS voluntary compliance

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-5...60 °C
temperatur	
Ambient temperature	-5...65 °C