



BRP651703HLAN

**External corner for BRP/BRHP/BRAP 65x170mm halogen free alu finish**

**Technical properties**

**Architecture**

Fixing mode Clamping

**Configuration**

Antibacterial treatment No

**Compatibility**

Product compatibility BRP/BRAP

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 68 mm

Length 120 mm

Trunking width 170 mm

**Cover, door**

Lid mounting External

Lid with softlip -

Number of lids mountable 1

**Materials**

Material group plastic

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 85 / 95 °

**Accessories included**

Accessory configuration Moulded

**Standards**

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Use conditions**

---

Operating temperature

-30...90 °C

**temperatur**

---

Ambient temperature

-30...90 °C