



BRP651703HLAN

External corner for BRP/BRHP/BRAP 65x170mm halogen free alu finish

Technical properties

Architecture

Fixing mode Clamping

Configuration

Antibacterial treatment No

Compatibility

Product compatibility BRP/BRAP

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 68 mm

Length 120 mm

Trunking width 170 mm

Cover, door

Lid mounting External

Lid with softlip -

Number of lids mountable 1

Materials

Colour aluminium

Material PC-ABS

Material group plastic

Installation, mounting

Base punching Without base punching

Settings

Angle range 85 / 95 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHS voluntary compliance

Use conditions

Operating temperature -30...90 °C

