



BRP651704HLAN

**Internal corner for BRP/BRHP/BRAP 65x170mm halogen free alu finish**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 65 mm

Trunking width 170 mm

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 85 / 95 °

**Accessories included**

Accessory configuration Moulded

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK07

**Use conditions**

Operating temperature -5...90 °C