



BRP651705HLAN

Flat angle for wall trunking BRP/BRAP/BRHP 65x170mm halogen free alu finish

Technical properties

Architecture

Fixing mode Clamping

Configuration

Antibacterial treatment No

Compatibility

Product compatibility BRP / BRAP

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 65 mm

Length 185 mm

Trunking width 170 mm

Cover, door

Lid with softlip -

Materials

Material group plastic

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHs voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK07

Use conditions

Operating temperature

-30...90 °C

temperatur

Ambient temperature

-30...90 °C