



BRS6517019010



## Trunking base, steel

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

Device installation compatible format	Standard 60mm, 45mm
---------------------------------------	---------------------

#### Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

#### Dimensions

Trunking height	68 mm
Length	2000 mm
Trunking width	170 mm

#### Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	29 / 42
--	---------

#### Cover, door

Lid mounting	Internal
Lid width	80 mm
Number of lids mountable	1

#### Materials

RAL colour	RAL 9010 - Pure white
Material	sheet steel
Material group	steel
Type of surface treatment	powder-coated

#### Installation, mounting

Base punching	With base punching
---------------	--------------------

#### Cable

Internal/useful cross section	10240 mm²
-------------------------------	-----------

#### Equipment

Number of plugable separators	1
Compartment quantity	1
Cable retainers per meter	0

#### Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

<b>Safety</b>	
Protection index IP	IP30
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
<b>Use conditions</b>	
Operating temperature	-5...90 °C