



DAP245700ELN



PacPost double 650 mm, Alu naturel anodized

Technical properties

Architecture

Fixing mode Screwed

Configuration

Module double side

Compatibility

Device installation compatible format 45x45 mm

Dimensions

Depth 130 mm

Installation height 650 mm

Pole shape rectangle

Width 68 mm

Materials

Colour aluminium

Material Aluminium

Material group aluminium

Type of surface treatment Anodised

Installation, mounting

Fixing type bottom punching

Cable

Internal/useful cross section 3600 mm²

Cable entry Bottom

Equipment

Number of fix dividers 2

Standards

European directive RoHS voluntary compliance