



DAP80650ELN



PacPost 80, 650 mm, Alu naturel anodized

Technical properties

Architecture

Fixing mode Screwed

Configuration

Module single side

Compatibility

Device installation compatible format Ecoline front mounting

Dimensions

Depth 65 mm

Installation height 650 mm

Length 650 mm

Pole shape rectangle

Width 98 mm

Materials

Colour aluminium

Material Aluminium

Material group aluminium

Type of surface treatment Anodised

Installation, mounting

Fixing type bottom punching

Cable

Internal/useful cross section 5400 mm²

Cable entry Bottom

Equipment

Number of fix dividers 1

Standards

European directive RoHS voluntary compliance