



DR32FT



Din rail board,2 row 32M, whole transparent door,flush

Technical properties

Architecture

Intended door position left

Configuration

Number of modules 32

Compatibility

Suitable for lightning protection Yes

Dimensions

Insertion depth 110 mm

Depth of wall niche 105 mm

Depth of installed product 5 mm

Internal depth 107 mm

Height of installed product 499 mm

Width of installed product 430 mm

Width in division units 16

Thickness of sidewall material 1.2 mm

Built-in width 400 mm

Cover, door

Material thickness cover 1.2 mm

Identification of protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door leave single

Cover type Cover

Transparent cover or door Yes

Materials

Copper weight of the product 0 kg

Colour light grey

Material quality Material mix

Surface appearance matt

Installation, mounting

Suitable for outdoor use No

Suitable for ground mounting No

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	2
Number of keys	1
Quantity of rails	2
On/Off switch	No
Number of openings for flange plates	2
Extension possible	Yes

Standards

Approvals	BS EN 61439-3
-----------	---------------

Safety

IK protection code against mechanical impacts	IK05
Protection class	isol.class I
Glow wire test	according to IEC 61439-1
RoHS conform	Yes
Halogen free	No
Fire resistance	-