



DR48S



**Din rail board, 3 row 48M, non-transparent door, surface**

**Technical properties**

**Architecture**

Intended door position left

**Configuration**

Number of modules 48

**Compatibility**

Suitable for lightning protection Yes

**Dimensions**

Insertion depth 110 mm

Depth of installed product 115 mm

Internal depth 107 mm

Height of installed product 624 mm

Width of installed product 405 mm

Width in division units 16

Thickness of sidewall material 1.2 mm

**Cover, door**

Material thickness cover 1.2 mm

Identification of protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door leave single

Cover type Cover

Transparent cover or door No

**Materials**

Copper weight of the product 0 kg

Colour light grey

Material Steel

Material quality Steel

Surface appearance matt

**Installation, mounting**

Suitable for outdoor use No

Suitable for ground mounting No

**Settings**

Enclosure type

Distributor empty cabinet

---

**Equipment**

Number of rows	3
Number of keys	1
Quantity of rails	3
On/Off switch	No
Number of openings for flange plates	2
Extension possible	Yes

---

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

---

**Safety**

IK protection code against mechanical impacts	IK05
Glow wire test	according to IEC 61439-1
Halogen free	No
Fire resistance	-