



DR80S



Din rail board, 5 row 80M, non-transparent door, surface

Technical properties

Architecture

Intended door position left

Configuration

Number of modules 80

Compatibility

Suitable for lightning protection Yes

Dimensions

Insertion depth 110 mm

Depth of installed product 115 mm

Internal depth 107 mm

Height of installed product 924 mm

Width of installed product 405 mm

Width in division units 16

Thickness of sidewall material 1.2 mm

Cover, door

Material thickness cover 1.2 mm

Identification of protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door leave single

Cover type Cover

Transparent cover or door No

Materials

Copper weight of the product 0 kg

Colour light grey

Material quality Steel

Surface appearance matt

Installation, mounting

Suitable for outdoor use No

Suitable for ground mounting No

Settings

Enclosure type Distributor empty cabinet

Equipment

Number of rows	5
Number of keys	1
Quantity of rails	5
On/Off switch	No
Number of openings for flange plates	2
Extension possible	Yes

Standards

Approvals	BS EN 61439-3
-----------	---------------

Safety

IK protection code against mechanical impacts	IK05
Protection class	isol.class I
Glow wire test	according to IEC 61439-1
Halogen free	No
Fire resistance	-