



DR96F



Din rail board, 6 row 96M, non-transparent door, flush

Technical properties

Architecture

Intended door position	left
------------------------	------

Configuration

Number of modules	96
-------------------	----

Compatibility

Suitable for lightning protection	Yes
-----------------------------------	-----

Dimensions

Insertion depth	110 mm
Depth of wall niche	105 mm
Depth of installed product	5 mm
Internal depth	107 mm
Height of installed product	1109 mm
Width of installed product	430 mm
Width in division units	16
Thickness of sidewall material	1.2 mm
Built-in width	400 mm

Cover, door

Material thickness cover	1.2 mm
Identification of protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door leave	single
Cover type	Cover
Transparent cover or door	No

Materials

Copper weight of the product	0 kg
Colour	light grey
Material quality	Steel
Surface appearance	matt

Installation, mounting

Suitable for outdoor use	No
Suitable for ground mounting	No

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	6
Number of keys	1
Quantity of rails	6
On/Off switch	No
Number of openings for flange plates	2
Extension possible	Yes

Standards

Approvals	BS EN 61439-3
-----------	---------------

Safety

IK protection code against mechanical impacts	IK05
Protection class	isol.class I
Glow wire test	according to IEC 61439-1
Halogen free	No
Fire resistance	-