



EC700

**Pulses concentrator**

**Technical properties**

**Configuration**

Number of modules	4
-------------------	---

**Main electrical features**

Rated operational voltage Ue	100 / 230 / 400 V
------------------------------	-------------------

**Electric current**

Number of entry circuits	7
--------------------------	---

**Dimensions**

Depth of installed product	50 mm
Height of installed product	90 mm
Length	73 mm
Width of installed product	67 mm
Width	90 mm

**Measurement**

Type of measuring instrument	digital
------------------------------	---------

**Installation, mounting**

Mounting type	din-Rail
---------------	----------

**Connection**

Type of Bus connexion	other
-----------------------	-------

**Equipment**

Interface type	other
----------------	-------

**Use conditions**

Operating temperature	-10...55 °C
Type of primary energy	Current
Storage/transport temperature	-20...70 °C