



EC700

Pulses concentrator

Technical properties

Configuration

Number of modules	4
-------------------	---

Main electrical features

Rated operational voltage U _e	100 / 230 / 400 V
--	-------------------

Electric current

Number of entry circuits	7
--------------------------	---

Dimensions

Depth of installed product	50 mm
Height of installed product	90 mm
Length	73 mm
Width of installed product	67 mm
Width	90 mm

Measurement

Type of measuring instrument	digital
------------------------------	---------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Type of Bus connexion	other
-----------------------	-------

Equipment

Interface type	other
----------------	-------

Use conditions

Operating temperature	-10...55 °C
Type of primary energy	Current
Storage/transport temperature	-20...70 °C