



EC700

## Pulses concentrator

### Technical properties

#### Architecture

Fixing mode Din-Rail

#### Configuration

Number of modules 4

#### Main electrical features

Rated operational voltage Ue 100 / 230 / 400 V

#### Electric current

Number of entry circuits 7

#### Dimensions

Depth of installed product 50 mm

Height of installed product 90 mm

Length 73 mm

Width of installed product 67 mm

Width 90 mm

#### Measurement

Type of measuring instrument digital

#### Installation, mounting

Mounting type din-Rail

#### Connection

Type of Bus connexion other

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -10...55 °C

Type of primary energy Current

Storage/transport temperature -20...70 °C