



EE003



Cell for twilight switch, wall mounted

Technical properties

Architecture

Fixing mode surface-mounting

Dimensions

Depth of installed product 37 mm

Height of installed product 32 mm

Length 89 mm

Width of installed product 48 mm

Power supply

Supply voltage 230 V +/- 10%

Materials

RAL colour RAL 7035 - Light grey

Lighting control

Brightness measurement range 5 / 2000 Lux

Installation, mounting

Mounting type surface-mounted

Connection

Conductor cross-section 0.75...4 mm²

Conductor cross-section (flexible) 0.75...4 mm²

Equipment

Probe type light sensor

Use conditions

Operating temperature -30...60 °C

Storage/transport temperature -30...60 °C

Identification

Main design line KNX