



EE632

LED floodlight 1200 Lumen with movement detector, white

Technical properties

Functions

Dimmer RF	No
Dimming 0-10 V	No
Dimmer DMX	No
Dimming GPRS	No
Dimming Zigbee	No
Dimming depending on control gear	No
Dimming LineSwitch	No
Dimming mains voltage modulation	No
Dimming potentiometer (integrated)	No
Dimming programmable	No
Dimming sine wave reduction	No

Main electrical features

Rated voltage	230...240 V
Type of supply voltage	AC

Dimensions

Height of installed product	140 mm
Length	100 mm
Built-in width	0 mm

Power

System rated power	12 W
--------------------	------

Power supply

Control gear type	Not required
-------------------	--------------

Materials

RAL colour	RAL 9010 - Pure white
Material	plastic
Surface appearance	glossy
Dominant light colour	white

Lighting control

Type of lamp	LED not exchangeable
Lamps capacity	12
Luminous flux	1200 lm

Installation, mounting

Suitable for ground mounting	No
Suitable for clamp-mounting	No
Suitable for light-track mounting	No
Can be suspended	No
Suitable for traverse mounting	No
Connection	
Suitable for through-wiring	Yes
Scope of delivery	
With lamp	Yes
Control gear included	No
Accessories included	
With light sensor	Yes
Equipment	
Type of dimmer	Yes
Colour rendering index (CRI)	80-89
Use	
Beam angle	$\geq 80^\circ < 360^\circ$
Light sharing	Symmetric
Safety	
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
Impact strength	IK04