



EEN002



## Cell for twilight switch, flush mounted

### Technical properties

#### Architecture

Fixing mode	Built-in installation
-------------	-----------------------

#### Dimensions

Depth of installed product	90 mm
Height of installed product	40 mm
Length	30 mm

#### Lighting control

Brightness measurement range	5 / 2000 Lux
------------------------------	--------------

#### Connection

Sensor cable length	1 m
Conductor cross-section	2 x 0.75 mm <sup>2</sup>

#### Settings

Delay ON	60 s
Delay OFF	80 s

#### Equipment

Probe type	light sensor
------------	--------------

#### Safety

RoHS conform	Yes
Halogen free	No

#### Use conditions

Operating temperature	-30...60 °C
Storage/transport temperature	-30...60 °C