



EEN002

IP55

Cell for twilight switch, flush mounted

Technical properties

Dimensions

Depth of installed product	90 mm
Height of installed product	40 mm
Length	30 mm

Lighting control

Brightness measurement range	5 / 2000 Lux
------------------------------	--------------

Installation, mounting

Mounting type	surface
---------------	---------

Connection

Sensor cable length	1 m
Conductor cross-section	2 x 0.75 mm ²

Cable

Wire	Cable length between twilight switch and brightness sensor max. 100 m
------	---

Settings

Delay ON	60 s
Delay OFF	80 s

Equipment

Probe type	light sensor
------------	--------------

Safety

RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-30...60 °C
Storage/transport temperature	-30...60 °C

Identification

Main design line	House electronics
------------------	-------------------