



EEN002



Cell for twilight switch, flush mounted

Technical properties

Dimensions

Depth of installed product	90 mm
Height of installed product	40 mm
Length	30 mm

Lighting control

Brightness measurement range	5 / 2000 Lux
------------------------------	--------------

Connection

Sensor cable length	1 m
Conductor cross-section	2 x 0.75 mm ²

Settings

Delay ON	60 s
Delay OFF	80 s

Equipment

Probe type	light sensor
------------	--------------

Use conditions

Operating temperature	-30...60 °C
Storage/transport temperature	-30...60 °C