



EG001

IP54

Radio antenna DCF77

Technical properties

Connectivity

Radio with radio receiver for the DCF77 signal

Dimensions

Dimensions (LLxwxh) 38 x 75 x 89 mm

Materials

Colour independent of design lines white

RAL colour RAL 9010 - Pure white

Installation, mounting

Bolted joint with wall bracket and screw fitting

Connection

Conductor cross-section (flexible) 0.5...1.5 mm²

Conductor cross-section (rigid) 0.5...2.5 mm²

Cable

Line length max. 200 m

Safety

Protection index IP IP54

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -20...50 °C

Storage/transport temperature -20...70 °C