



EK081

## Fixed ambient probe 10 Ohm

### Technical properties

#### Configuration

Configuration configuration for connected thermostat adjustable via DIP-switch

#### Compatibility

Compatible with EK186 / EK187/ EG502

#### Length

Maximum connection distance between receiver and transmitter 50m

#### Resistance

Characteristic resistance value at 25 °C 11580 Ω

#### Installation, mounting

Installation mode suitable for surface mounting or for mounting on flush-mounted boxes

#### Connection

Sensor cable length max. 50 m

Probe conductor cross-section (recommended) 1.5 mm<sup>2</sup>

#### Equipment

Probe type adjustable room sensor

#### Safety

RoHS conform Yes

#### Use conditions

Operating temperature 0...80 °C