



EK081



Fixed ambient probe 10 Ohm

Technical properties

Configuration

Configuration configuration for connected thermostat adjustable via DIP-switch

Compatibility

Compatible with EK186 / EK187/ EG502

Resistance

Characteristic resistance value at 25 °C 11580 Ω

Connection

Sensor cable length max. 50 m

Probe conductor cross-section (recommended) 1.5 mm²

Equipment

Probe type adjustable room sensor

Safety

Protection index IP IP30

Use conditions

Operating temperature 0...80 °C